



Pass and Seymour  
Non-Fusible Mechanical Interlock  
Part No. PS5100MIR7W



Four pole, Five wire, Non-Fusible Mechanical Interlock Receptacle. 100 amp, 3Y, 277/480 vac.

### Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

### Specifications

#### General Info

Color	Gray	UPC Number	785007015683
Country Of Origin	United States	Product Line	Pass & Seymour
Application Sector	Industrial	Standard	UL Listed

#### Technical Information

Number of Poles	4-Way	Voltage	277 V
Phase	3	Number of Wires	5