



4-Pole, 5-Wire, Pin and Sleeve Receptacle. 20A, 3Y, 120/208V.



## Features & Benefits

All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.

And all feature chemical-resistant thermoplastic construction.

An exclusive, hinged cord grip eliminates loose parts that get lost.

North American products come completely ready to wire, for quick, simple installation.

Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Gray       |
| Country Of Origin | United States  | Application Sector | Industrial |
| Standard          | UL Listed      |                    |            |

### Dimensions

|                   |         |                   |        |
|-------------------|---------|-------------------|--------|
| Product Width US  | 2.5 in  | Product Height US | 3.1 in |
| Product Length US | 3.17 in |                   |        |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 151348 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Technical Information

|                 |       |          |       |
|-----------------|-------|----------|-------|
| Number of Wires | 5     | Amperage | 20 A  |
| Number of Poles | 4-Way | Voltage  | 120 V |