



Pass and Seymour  
15A, 125V Extra-Hard Use Spec-Grade Connector, Black and White  
Part No. PS5269X

Straight Blade Connector 2-Pole 3-Wire 15A 125A



## Features & Benefits

Unit arrives completely ready-to-wire, cuts installation time significantly.

Nylon housing provides impact and chemical resistance.

Rugged two-piece cord grip provides more uniform cord retention.

Internal dust shield keeps terminals free of contaminants.

Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.

All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.

Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.

Cord-grip screws recessed to protect installer against screwdriver head slippage.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007237306	Country Of Origin	Mexico
Features	Chemical Resistant	Application Sector	Industrial
Standard	UL 498	Warranty Type	1-Year
Type	Connector		

### Dimensions

Product Width US	1.516 in	Product Length US	2.638 in
------------------	----------	-------------------	----------

### Additional Information

Product Environmental Profile Yes

### Technical Information

---

Connector Style	Straight Blade	Flanged	No
Terminal Accommodation	#4 AWG	Connection	Wire Grounding
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Voltage	125.0 V

---