



Straight Blade Connector 2-Pole 3-Wire 15A 125A

## Features & Benefits

Unit arrives completely ready-to-wire, cuts installation time significantly.

Rugged two-piece cord grip provides more uniform cord retention.

Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.

Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Nylon housing provides impact and chemical resistance.

Internal dust shield keeps terminals free of contaminants.

All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.

Cord-grip screws recessed to protect installer against screwdriver head slippage.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007237313	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498, FEDSPEC
Type	Straight Blade		

### Dimensions

Product Width US	1.516 in	Product Length US	2.638 in
------------------	----------	-------------------	----------

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

Technical Information

---

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 10 AWG

---