



Pass and Seymour
Straight Blade CONN 3W 15A 125V HG PS5269XHG
Part No. PS5269XHG



Straight Blade Connector 2-Pole 3-Wire 15A 125V
Hospital Grade

Features & Benefits

Unit arrives completely ready-to-wire, cuts installation time significantly.

Nylon housing provides impact and chemical resistance.

Rugged two-piece cord grip provides more uniform cord retention.

Internal dust shield keeps terminals free of contaminants.

Tri-drive assembly screws are standard on Hospital Grade plugs and connectors (angle plugs not included).

All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.

Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.

Cord-grip screws recessed to protect installer against screwdriver head slippage.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL498		

Dimensions

Product Width US	1.358 in	Product Length US	2.638 in
------------------	----------	-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 0 AWG
Voltage	125.0 V		
