



Pass and Seymour Non-Fusible Mechanical Interlock Part No. PS530MIR5W



Four pole, Five wire, Non-Fusible Mechanical Interlock Receptacle. 30 amp, 3Y, 347/600 vac.

Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

Color	Gray	UPC Number	785007420524
Country Of Origin	United States	Product Line	Pass & Seymour
Application Sector	Industrial	Standard	UL Listed

Technical Information

Number of Poles	4-Way	Voltage	347 V
Phase	3	Number of Wires	5