



4-Pole, 5-Wire, Non-Fusible Mechanical Interlock Receptacle. 30A, 3Y, 347/600V.

## Features & Benefits

- Top or Bottom feed. Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate. No closure plug kits required.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007420524	Country Of Origin	United States
Application Sector	Industrial	Standard	UL Listed

### Technical Information

Phase	3	Number of Wires	5
Number of Poles	4-Way	Voltage	347 V