



Pass and Seymour
20A, 125V Extra-Hard Use Hospital-Grade Angled Plug, Black and Clear
Part No. PS5366HGAN



Straight Blade Plug 2-Pole 3-Wire 20A 125A

Features & Benefits

Angle plugs and adapters both allow for 4-position face rotation.

Tri-drive assembly and cord-grip screws are standard on all angle adapters.

Angle adapter (sold separately as catalog number EHU15AN) retrofits on all Pass & Seymour EHU-style Straight Blade plugs and connectors. Simply remove the straight handle body from the plug or connector face assembly and replace with the angle adapter.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007236781	Country Of Origin	Mexico
Features	Chemical Resistant, Durable, Dust Resistant	Application Sector	Commercial
Standard	UL 498, FEDSPEC	Warranty Type	1-Year
Type	Plug		

Dimensions

Product Width US	1.53 in	Product Depth US	1.35 in
Product Height US	2.13 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connector Style	Straight Blade	Flanged	No
-----------------	----------------	---------	----

Terminal Accommodation	#18 AWG - #10 AWG	Number of Wires	3
------------------------	-------------------	-----------------	---

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20P
----------------	--------	-------------------------	-------

Voltage	125.0 V		
---------	---------	--	--