



Pass and Seymour  
20A, 250V Extra-Hard Use Hospital-Grade Angled Plug, Black and Clear  
Part No. PS5466HGAN



STR BLD ANGLE PLUG 3W 20A 250V HG

## Features & Benefits

Angle plugs and adapters both allow for 4-position face rotation.

Tri-drive assembly and cord-grip screws are standard on all angle adapters.

Angle adapter (sold separately as catalog number EHU15AN) retrofits on all Pass & Seymour EHU-style Straight Blade plugs and connectors. Simply remove the straight handle body from the plug or connector face assembly and replace with the angle adapter.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007236828	Country Of Origin	Mexico
Features	Chemical Resistant, Durable, Dust Resistant	Application Sector	Commercial
Standard	UL 498, FEDSPEC	Warranty Type	1-Year
Type	Plug		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

Connector Style	Straight Blade	Flanged	No
Terminal Accommodation	#18 AWG - #10 AWG	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	6-20P
Voltage	250.0 V		