



4-Pole, 5-Wire, Non-Fusible Mechanical Interlock Receptacle. 60A, 3Y, 120/208V

Features & Benefits

- Top or Bottom feed. Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate. No closure plug kits required.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007420647	Country Of Origin	United States
Application Sector	Industrial	Standard	UL Listed

Technical Information

Phase	3	Number of Wires	5
Number of Poles	4-Way	Voltage	120 V