

Replacement Plug Front Body, 5-Wire 60A 3-Phase 347/600V.



Features & Benefits

All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.

North American products come completely ready to wire, for quick, simple installation. And all feature chemical-resistant thermoplastic construction.

Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.

An exclusive, hinged cord grip eliminates loose parts that get lost.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|---------------|
| Product Line | Pass & Seymour | Country Of Origin | United States |
| Application Sector | Industrial | Standard | UL Listed |
| Type | Plug Tail | | |

Dimensions

| | | | |
|-------------------|--------|------------------|---------|
| Product Width US | 4.5 in | Product Depth US | 10.0 in |
| Product Height US | 4.5 in | | |

Technical Information

| | | | |
|-----------------|-------|----------|---------|
| Number of Wires | 5 | Amperage | 60 A |
| Number of Poles | 4-Way | Voltage | 347.0 V |