



Pass and Seymour
MaxGrip M3 Connector, Yellow
Part No. PS5669Y



Straight Blade Connector 2-Pole 3-Wire 15A 250V

Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Enclosed terminals provide solid, internally-clamped connections.

Molded finger grips promote safe, sure handling.

High-visibility yellow and orange, or gray.

Hospital Grade version displays the Hospital Grade green dot.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007237627	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498, FEDSPEC
Type	Straight Blade		

Dimensions

Product Width US	1.34 in	Product Depth US	1.21 in
Product Length US	1.83 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 10 AWG