



Pass and Seymour  
MaxGrip M3 Plug, Gray  
Part No. PS5965GRY



Straight Blade Plug 2-Pole 3-Wire 15A 125V

## Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Enclosed terminals provide solid, internally-clamped connections.

Molded finger grips promote safe, sure handling.

High-visibility yellow and orange, or gray.

Hospital Grade version displays the Hospital Grade green dot.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Gray       |
| Country Of Origin | Mexico         | Application Sector | Industrial |
| Standard          | UL listed      | Type               | Plug Tail  |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.34 in | Product Depth US | 1.21 in |
| Product Height US | 1.83 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

## Technical Information

---

|                 |             |           |            |
|-----------------|-------------|-----------|------------|
| Number of Wires | 3           | Amperage  | 15 A       |
| Number of Poles | Double Pole | Wire Size | 14 - 0 AWG |
| Voltage         | 125.0 V     |           |            |

---