



Pass and Seymour
15A, 125V Hospital-Grade MaxGrip M3 Plug, Gray
Part No. PS8115



STR BLD PLUG 3W 15A125A HG

Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Enclosed terminals provide solid, internally-clamped connections.

Molded finger grips promote safe, sure handling.

High-visibility yellow and orange, or gray.

Hospital Grade version displays the Hospital Grade green dot.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498		

Dimensions

Product Width US	1.34 in	Product Depth US	1.21 in
Product Height US	1.83 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Voltage	125.0 V		
