



Pass and Seymour
20A 125V Heavy Duty Hospital-Grade Duplex Receptacle, Back and Side Wire, Red
Part No. PS8300HRED



Heavy-Duty Hospital Grade Duplex Receptacle Back and Side Wire 20A 125V

Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Two drive screws anchor strap to back body and face.

Tri-drive brass terminal screws.

Two back wire holes for more wiring flexibility.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Finish	Matte	UPC Number	785007860054
Country Of Origin	Mexico	Number of Receptacles	2
Application Sector	Commercial, Hospital Grade	Standard	UL498, CSA C22.2 No. 42, FEDSPEC
Type	Outlet		

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Temperature Rating	-40° - 60° C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor