



Spec Grade Decorator Combination Hallway Light & Single Receptacle Back & Side Wire 20amp 120/125VAC White

Features & Benefits

- Impact-resistant face and body.
- External screw-pressure-plate back and side wired.
- Ground screw position under the end of the strap minimizes the risk of contact.
- Sensor automatically turns light ON in the dark.
- Light sensor for enhanced sensitivity.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.
- GE Lexan: high impact-resistant lens.
- Accepts #12 and #14 AWG.
- Energy-efficient LED has average 20-year life expectancy: eliminates bulb replacement.
- Increased light output for better illumination.
- For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	NTL885TRWCC6
Color	White	Country Of Origin	China
Application Sector	Commercial	Standard	cULus UL498

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connection	Back and side wire	Amperage	20 A
Number of Poles	Double Pole	Voltage	120.0 V
Environmental Conditions	Flammability: UL94 V2		