



Pass and Seymour  
15A NEMA L715 Plug - Black Back, White Front Body  
Part No. PSL715P

Turnlok® Plug 3-Wire 15A 277V



## Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.

Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Raised ribs provide non-slip gripping profile for turning to lock and unlock.

Double dovetail design provides superior protection against cord pull-out forces.

Impact- and corrosion-resistant durable nylon 6/6 shell material.

Rounded back contour reduces snags and hang-ups on the job site.

Scallop shell design provides non-slip gripping surface for insertion and withdrawal.

Visible stamped NEMA configuration and device rating.

New-design external cord grips provide visible assurance of safe and proper cord retention.

Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007236613	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL 498

### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

### Additional Information

---

Product Environmental Profile      Yes

---

**Technical Information**

---

Number of Wires                      3                                      Number of Poles                      Double Pole

---

Wire Size                                      4                                      Voltage                                      277 V

---