



15A GFCI works with the existing three-wire PlugTail connectors creating a non-feed thru application for facility owners. At rough-in, just install the same right-angle connector for GFCI and receptacle openings. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock® Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected	Faster, more reliable installation
No exposed terminals create a finger-safe application before, during, and after installation	Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector
GFCI works with the existing 3-wire PlugTail connectors creating a non-feed-through application for facility	Zinc-plated steel mounting strap

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Commercial, GFCI, Indoor, Self-Test, Tamper-Resistant	Application Sector	Residential/Commercial
Standard	cULus, UL Listed, FSUL	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.72 in	Product Depth US	1.2 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Interrupt Rating	4 A
Frequency Rating	60 Hz	Trip Range	5±1 mA

Connection	Built-in Connector	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Voltage	125.0 V	Environmental Conditions	95% Humidity, UL 94 V2