



Pass and Seymour
Discontinued - PlugTail® Three-Way 15A Toggle Switch, Ivory
Part No. PT15AC3I



PlugTail® Three-Way Toggle Switch, 15amp 120/277vac, Ivory

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Shallow design for easier installation.

No exposed terminals create a finger-safe application before, during, and after installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Impact- and chemical- resistant cover.

One-piece nickel-plated mounting strap for superior corrosion resistance.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------------|------------------------|
| Product Line | Pass & Seymour | Replaced by Part Number | PT20AC3I |
| Color | Ivory | Finish | Matte |
| UPC Number | 785007108354 | Country Of Origin | Mexico |
| Features | PlugTail | Switch Type | Toggle |
| Number of Switches | 1 | Application Sector | Commercial, Industrial |

| | | | |
|---------------------------------------|-------------------------|------------------------|-------------------|
| Wall Plate Included | No | Standard | FEDSPEC |
| Warranty Type | 1-Year Limited Warranty | Type | Switch |
| Listing Agencies / 3rd Party Agencies | | | |
| cULus ListingNumber | 140597 | cULus Listed | Yes |
| Technical Information | | | |
| Connection Location | Back Only | Terminal Accommodation | #14 AWG - #12 AWG |
| Number of Gangs | 1 | Throw Type | Single Throw |
| Amperage | 15 A | Number of Poles | 3-Way |
| Requires Neutral Wire | No | Indoor/Outdoor | Indoor |
| Mounting Type | Wall Box | Wire Connection Type | PlugTail |
| Voltage | 120/277 V | | |