



Pass and Seymour
PlugTail® Hospital-Grade Tamper-Resistant 20A Self-Test Night Light/GFCI, White
Part No. PT2097HGNTLTRW



The fastest-installing GFCI ever now conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock® Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected. For detailed PlugTail information, visit our PlugTail Headquarters. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Specifications

General Info

Color	White	UPC Number	785007048179
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Standard	cULus, UL Listed, FSUL

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Poles	Double Pole	Voltage	125 V
Trip Range	4 to 6 mA	Connection	Built-in Connector
Frequency Rating	60 Hz	Interrupt Rating	4 A
Environmental Conditions	95% Humidity, UL 94 V2		