



Pass and Seymour
PlugTail® Hospital Grade 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, White
Part No. PT2097HGW



PlugTail® Hospital-Grade 20A Self-Test GFCI Receptacle. Self-test GFCI Technology - conducts an automatic test every three seconds, ensuring it's always ready to protect. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Plated steel wrap strap design for maximum durability and corrosion resistance.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	Commercial, GFCI, Indoor, Self-Test
Application Sector	Residential/Commercial	Standard	cULus, UL Listed, FSUL
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.72 in	Product Depth US	1.2 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Interrupt Rating	4 A	Frequency Rating	60 Hz
Trip Range	5±1 mA	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Voltage	125.0 V		