



PlugTail® Spec-Grade Tamper-Resistant 20A Self-Test Duplex GFCI. Self-test GFCI Technology - conducts an automatic test every three seconds, ensuring it's always ready to protect. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Plated steel wrap strap design for maximum durability and corrosion resistance.

Specifications

General Info

| | | | |
|-------------------|---|-----------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | China | Number of Receptacles | 2 |
| Outlet Type | GFCI, Indoor, Residential, Tamper-Resistant | Application Sector | Residential/Commercial |
| Standard | cULus, UL Listed, FSUL | Warranty Type | 1-Year Limited Warranty |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 1.72 in | Product Depth US | 1.2 in |
| Product Height US | 4.2 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|---------------------|--------------------|------------------|-----------|
| Is Tamper-Resistant | Yes | Interrupt Rating | 4 A |
| Frequency Rating | 60 Hz | Trip Range | 4 to 6 mA |
| Connection | Built-in Connector | Number of Gangs | 1 |
| Amperage | 20 A | Mounting Type | Box |

| | | | |
|---------|-------|--------------------------|------------------------|
| Voltage | 125 V | Environmental Conditions | 95% Humidity, UL 94 V2 |
|---------|-------|--------------------------|------------------------|