Pass and Seymour
PlugTail® Single Pole 20A Toggle Switch, Gray
Part No. PT20AC1GRY

PlugTail® Single-Pole 20A Toggle Switch

Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Shallow design for easier installation.

No exposed terminals create a finger-safe application before, during, and after installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Impact- and chemical- resistant cover.

One-piece nickel-plated mounting strap for superior corrosion resistance.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	Mexico	Application Sector	Commercial
Standard	cULus, WS8996		

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in

Product Height US	2.375 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes

Technical Information

Contact Rating	20amp, 120/277vac	Closed Contact Resistance	Toggle
Amperage	20 A	Number of Poles	Single Pole
Wattage	1 W	Voltage	120.0 V