



Legrand
PlugTail® Three-Way 20 amp Toggle Switch, Gray
Part No. PT20AC36RY



PlugTail information, visit our PlugTail Headquarters.

Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Shallow design for easier installation.

No exposed terminals create a finger-safe application before, during, and after installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Impact- and chemical- resistant cover.

One-piece nickel-plated mounting strap for superior corrosion resistance.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	Gray
UPC Number	785007108477
Country Of Origin	Mexico
Product Line	Pass & Seymour
Application Sector	Commercial
Standard	cULus, WS8996

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
cULus ListingNumber	140597

Technical Information

Wattage	3 W
---------	-----

Number of Poles	3-Way
------------------------	-------

Voltage	120 V
----------------	-------

Closed Contact Resistance	Toggle
----------------------------------	--------

Contact Rating	20amp, 120/277vac
-----------------------	-------------------
