



**Legrand**  
PlugTail® Three-Way 20 amp Toggle Switch, Ivory  
Part No. PT20AC3I



PlugTail information, visit our PlugTail Headquarters.

## Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Shallow design for easier installation.

No exposed terminals create a finger-safe application before, during, and after installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Impact- and chemical- resistant cover.

One-piece nickel-plated mounting strap for superior corrosion resistance.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Color	Ivory
UPC Number	785007108460
Country Of Origin	Mexico
Product Line	Pass & Seymour
Application Sector	Commercial
Standard	cULus, WS8996

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
cULus ListingNumber	140597

### Technical Information

Wattage	3 W
---------	-----

---

<b>Number of Poles</b>	3-Way
------------------------	-------

---

<b>Voltage</b>	120 V
----------------	-------

---

<b>Closed Contact Resistance</b>	Toggle
----------------------------------	--------

---

<b>Contact Rating</b>	20amp, 120/277vac
-----------------------	-------------------

---