



Pass and Seymour
PlugTail® Specification Grade Three-Way Illuminated 20A Toggle Switch, Ivory
Part No. PT20AC3ISL



3-way Illuminated Toggle Switch, 20A 120/277VFor detailed PlugTail information, visit our PlugTail Headquarters.

Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.	Impact- and chemical- resistant cover.
Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.	One-piece nickel-plated mounting strap for superior corrosion resistance.
Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.	Auto-ground clip assures positive ground.
Shallow design for easier installation.	Heavy-duty bumpers for quiet, smooth operation.
No exposed terminals create a finger-safe application before, during, and after installation.	For covering patents, see www.legrand.us/patents .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .	

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL 20		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Actuator	Toggle	Contact Rating	120/277vac, 20amp
Amperage	20 A	Action	DPDT
Number of Poles	Double Pole	Voltage	120.0 V
