



Pass and Seymour PlugTail® Specification Grade Three-Way Illuminated 20 amp Toggle Switch, Ivory Part No. PT20AC3ISL



Three-Way Illuminated Toggle Switch, 20amp 120/277volt, White For detailed PlugTail information, visit our PlugTail Headquarters.

Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Shallow design for easier installation.

No exposed terminals create a finger-safe application before, during, and after installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Impact- and chemical- resistant cover.

One-piece nickel-plated mounting strap for superior corrosion resistance.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	Ivory	UPC Number	785007108538
-------	-------	------------	--------------

Country Of Origin	Mexico	Product Line	Pass & Seymour
-------------------	--------	--------------	----------------

Application Sector	Residential/Commercial	Standard	UL 20
--------------------	------------------------	----------	-------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140597
--------------	-----	---------------------	--------

Technical Information

Number of Poles	Double Pole	Voltage	120 V
-----------------	-------------	---------	-------

Actuator	Toggle	Contact Rating	20amp, 120/277vac
----------	--------	----------------	-------------------

Action	dptd
--------	------