



Pass and Seymour
PlugTail® Three-Way 20A Decorator Switch, Ivory
Part No. PT2623I



For detailed PlugTail information, visit our [PlugTail Headquarters](#).

Features & Benefits

Ground wire pre-mounted to the box

4" square x 1 1/2" or 2 1/8" metal boxes

All Double Gang Kits contain two right angle PlugTail connectors

Mud ring factory installed

PlugTail Right Angle Connectors with 12 AWG copper pigtails

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007001051
Country Of Origin	Mexico	Features	Decorator Style
Application Sector	Industrial	Standard	UL 20
Type	Switch		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Amperage	20 A	Number of Poles	3-Way
----------	------	-----------------	-------

Wire Size	#14 - #10 AWG	Voltage	120/277 V
-----------	---------------	---------	-----------