



Pass and Seymour  
**PlugTail® Heavy Duty Spec Grade Plug Load Controllable Receptacle, 15A, 125V, White**  
Part No. PT26252SCCTW



These durable, dependable receptacles feature a permanently marked, differentiated solution that meets all necessary code requirements. For detailed PlugTail® information, visit our PlugTail® Headquarters.

## Features & Benefits

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Plated steel wrap strap design for maximum durability and corrosion resistance.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Permanent controlled markings on face of receptacle compliant with ASHRAE 90.1, CA Title 24, and NEC.

Auto-ground clip assures positive ground.

Half-controlled versions include welded, pre-wired lead that control top half of receptacle for split circuit applications.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico		

### Dimensions

Product Width US	1.5 in	Product Depth US	0.625 in
Product Height US	2.75 in		

### Listing Agencies / 3rd Party Agencies

---

cULus Listed

Yes

---

Technical Information

---

Amperage

15 A

---