



Pass and Seymour  
Discontinued - PlugTail® 15A 125V Spec-Grade Duplex Receptacle, Light Almond  
Part No. PT5262LA



PlugTail® Spec Grade Duplex Receptacle 15amp 125volt Light Almond

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

### Features & Benefits

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see [www.legrand.us/patents](#).

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only
- Illuminated face indicates power to receptacle and makes it easy to identify receptacle in dark applications.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Auto-ground clip assures positive ground.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

### Specifications

#### General Info

Product Line	Pass & Seymour	Replaced by Part Number	5262LA
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor	Type	Outlet

#### Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

#### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

Technical Information

---

Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	Voltage	125.0 V

---