




PlugTail  Spec Grade Duplex Receptacle 15amp 125volt Light Almond

For detailed PlugTail  information, visit our [PlugTail Headquarters](#).

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention. Illuminated face indicates power to receptacle and makes it easy to identify receptacle in dark applications.

No exposed terminals create a finger safe application before, during, and after installation. Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Crimped and welded contacts.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed. Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

## Specifications

### General Info

|                   |                    |                         |        |
|-------------------|--------------------|-------------------------|--------|
| Product Line      | Pass & Seymour     | Replaced by Part Number | 5262LA |
| Country Of Origin | Mexico             | Number of Receptacles   | 2      |
| Outlet Type       | Commercial, Indoor | Type                    | Outlet |

### Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 1.322 in | Product Depth US | 0.78 in |
| Product Height US | 2.635 in |                  |         |

### Listing Agencies / 3rd Party Agencies

---

---

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

#### Technical Information

---

|                |        |                 |             |
|----------------|--------|-----------------|-------------|
| Amperage       | 15 A   | Number of Poles | Double Pole |
| Indoor/Outdoor | Indoor | Voltage         | 125.0 V     |

---