



Pass and Seymour

PlugTail® Extra Heavy-Duty Surge Protective Duplex Receptacle, White
Part No. PT5262WSP

PlugTail information, visit our PlugTail Headquarters.



Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Plated steel wrap strap design for maximum durability and corrosion resistance.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Large brass contacts snugly terminate on device blade terminals.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

UPC Number	785007020939	Country Of Origin	China
Product Line	Pass & Seymour	Application Sector	Residential/Commercial
Standard	CSA Listed, cUL, UL Listed, RoHS, FSUL		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Voltage	125 V	Connection	Built-In Connector
Class	IG	Frequency Rating	60 Hz Hz
Phase	Single	Environmental Conditions	UL94 V2
Type of Indicators	LED, Audible Alarm		