



Pass and Seymour
PlugTail® Extra Heavy Duty Surge Protective Duplex Receptacle, Gray
Part No. PT5362GRYSP

PlugTail information, visit our PlugTail Headquarters.



Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

Plated steel wrap strap design for maximum durability and corrosion resistance.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007019940
Country Of Origin	China	Application Sector	Commercial, Residential
Standard	CSA Listed, cUL, UL Listed, RoHS, FSUL		

Dimensions

Product Width US	1.7 in	Product Depth US	1.2 in
Product Height US	2.75 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Phase	Single	Connection	Built-in Connector
Class	IG	Amperage	20 A
Type of Indicators	Audible Alarm, LED	Environmental Conditions	UL94 V2
