



## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.	Plated steel wrap strap design for maximum durability and corrosion resistance.
No exposed terminals create a finger safe application before, during, and after installation.	Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
Crimped and welded contacts.	Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
Large brass contacts snugly terminate on device blade terminals.	Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
Auto-ground clip assures positive ground.	For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click <a href="#">here</a> .	

## Specifications

General Info			
Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Phase	3	Number of Wires	3

Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	125.0 V