



Pass and Seymour PlugTail® Extra Heavy-Duty Hospital Grade Illuminated Receptacles, 15A, 125V, Red Part No. PT8200ILRED

PlugTail® Extra Heavy-Duty Hospital Grade Illuminated Duplex Receptacle, 15 A 125 V, Light Almond
For detailed PlugTail® information, visit our PlugTail® Headquarters.



Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Plated steel wrap strap design for maximum durability and corrosion resistance.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	Red	UPC Number	785007238655
-------	-----	------------	--------------

Country Of Origin	Mexico	Product Line	Pass & Seymour
-------------------	--------	--------------	----------------

Application Sector	Commercial	Standard	UL 498
--------------------	------------	----------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

Technical Information

Number of Poles	Double Pole	Voltage	125 V
-----------------	-------------	---------	-------

Phase	3	Wire Size	10-14Awg
-------	---	-----------	----------

Number of Wires	3
-----------------	---