



Pass and Seymour
PlugTail® Hospital Grade Extra Heavy Duty Surge Protective Duplex Receptacle, Ivory
Part No. PT8200ISP



PlugTail® Hospital Grade Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). 15 A 125 V, Ivory . For detailed PlugTail® information, visit our PlugTail® Headquarters.

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Plated steel wrap strap design for maximum durability and corrosion resistance.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Large brass contacts snugly terminate on device blade terminals.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Application Sector	Residential/Commercial	Standard	CSA Listed, cUL, UL Listed, RoHS, FSUL

Dimensions

Product Width US	1.5 in	Product Depth US	0.625 in
Product Height US	2.75 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Phase	Single	Frequency Rating	60 Hz
-------	--------	------------------	-------

Connection	Built-In Connector	Class	IG
------------	--------------------	-------	----

Amperage	15 A	Type of Indicators	Audible Alarm, LED
----------	------	--------------------	--------------------

Voltage	125.0 V	Environmental Conditions	UL94 V2
---------	---------	--------------------------	---------
