



PlugTail® Isolated Ground Decorator Spec Grade Receptacles, 20A, 125A



Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Plated steel wrap strap design for maximum durability and corrosion resistance.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Large brass contacts snugly terminate on device blade terminals.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007307818	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498, FEDSPEC

Dimensions

Product Width US	1.5 in	Product Depth US	0.625 in
Product Height US	3.281 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Phase	Three	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG		