



Pass and Seymour
PlugTail® Connectors, Right Angle, Solid, 6"
Part No. PTR6SOL



PlugTail® Connectors, Right Angle, Solid, 6-inch

Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Large brass contacts snugly terminate on device blade terminals.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Available in any wire length up to 25 inches, use Configurable Solutions to order.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007044553
Country Of Origin	China	Application Sector	Commercial
Standard	cULus UL498		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Number of Wires	3
---------------------	--------------------------	-----------------	---

Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact	Number of Poles	Double Pole
Wire Size	PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid, for use with PlugTail Receptacles only	Environmental Conditions	Flammability: UL94 V2
