



Legrand
PlugTail® Connectors, Right Angle, Solid, 25"
Part No. PTR6SOLB25



PlugTail® Connectors Right Angle Solid 25" For detailed PlugTail® information, visit our PlugTail® Headquarters.

Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Large brass contacts snugly terminate on device blade terminals.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

Available in any wire length up to 25 inches, use Configurable Solutions to order.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

UPC Number 785007044560

Countries Of Origin Mexico

Product Line Pass & Seymour

Application Sector Commercial

Standard cULus UL498

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

cULus ListingNumber 140596

Technical Information

Number of Poles Double Pole

Dielectric Strength Withstands 2000V minimum

Temperature Rating Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Wire Size PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid, for use with PlugTail Receptacles only

Number of Wires 3

Environmental Conditions Flammability: UL94 V2
