



Pass and Seymour
PlugTail® Connectors, Right Angle with Ground Screw, Solid, 6"
Part No. PTR6SOLG



PlugTail® Connectors Right Angle with Ground Screw Solid 6" For detailed PlugTail® information, visit our PlugTail® Headquarters.

Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Large brass contacts snugly terminate on device blade terminals.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Available in any wire length up to 25 inches, use Configurable Solutions to order.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

| | | | |
|--------------|----------------|--------------------|------------|
| UPC Number | 785007242751 | Country Of Origin | Mexico |
| Product Line | Pass & Seymour | Application Sector | Commercial |
| Standard | cULus UL498 | | |

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

| | | | |
|-----------------|-------------|---------------------|--------------------------|
| Number of Poles | Double Pole | Dielectric Strength | Withstands 2000V minimum |
|-----------------|-------------|---------------------|--------------------------|

| | | | |
|--------------------|---|--------------------------|--|
| Temperature Rating | <p>Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.</p> <p>Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact</p> | Wire Size | <p>PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid, for use with PlugTail Receptacles only</p> |
| Number of Wires | 3 | Environmental Conditions | <p>Flammability: UL94 V2</p> |
