



Pass and Seymour  
**PlugTail® Connector in Orange, Right Angle, Solid, 6-in XHHW-2 Wire**  
Part No. PTR6SOLOR



PlugTail® Connectors, Right Angle, Solid, 6-inch PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. Orange connector makes identifying isolated ground circuits easier.

## Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Distinguished orange connector head to help identify isolated ground circuits during rough in or device replacement.

PlugTail™ Orange Connector: #12 AWG, THHN, copper conductor, 6 - in leads, stripped, solid, for use with PlugTail Receptacles only

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007432633	Country Of Origin	Mexico
Features	Plug-In, Right Angle	Application Sector	Commercial
Standard	RoHS, cULus	Warranty Type	1-Year

### Dimensions

Product Width US	1.0 in	Product Weight US	0.06 lb
Product Height US	1.0 in	Product Length US	6.0 in

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Seismic Tested	No	Wire Size	12 AWG
----------------	----	-----------	--------

Indoor/Outdoor	Indoor	Connection Type	Wired
----------------	--------	-----------------	-------

Environmental Conditions	0 to 95% (relative humidity, non-condensing)
--------------------------	--