



PlugTail® Connectors Right Angle Stranded 25"" For detailed PlugTail® information, visit our PlugTail® Headquarters.

## Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Large brass contacts snugly terminate on device blade terminals.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Available in any wire length up to 25 inches, use Configurable Solutions to order.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

UPC Number	785007044577	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Commercial
Standard	cULus UL498		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

### Technical Information

Number of Poles	Double Pole	Dielectric Strength	Withstands 2000V minimum
-----------------	-------------	---------------------	--------------------------

---

Temperature Rating	<p>Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.</p> <p>Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact</p>	Wire Size	<p>PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, stranded, for use with PlugTail Receptacles only</p>
--------------------	---	-----------	---

---

Number of Wires	3	Environmental Conditions	Flammability: UL94 V2
-----------------	---	--------------------------	-----------------------

---