



Pass and Seymour
PlugTail® Connector in Orange, Right Angle, Stranded, 6-in XHHW-2 Wire
Part No. PTR6STRX22OR



PlugTail® Connectors, Right Angle, Stranded, 6-inch PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. Orange connector makes identifying isolated ground circuits easier. Utilizes XHHW-2 wire.

Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Utilizes XHHW-2 wire which is a thermoset insulated with XLPE (cross-linked Polyethylene).

For low leakage circuits.

Wire temperature rated 90°C Wet/Dry.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Distinguished orange connector head to help identify isolated ground circuits during rough in or device replacement.

Substantially higher insulation resistance than THHN wire and does not have PVC in insulation.

PlugTail™ Orange Connector: #12 AWG, XHHW - 2, copper conductor, 6 - in leads, stripped, stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007432770	Country Of Origin	Mexico
Features	Plug-In, Right Angle	Application Sector	Commercial
Standard	RoHS, cULus	Warranty Type	1-Year

Dimensions

Product Width US	1.0 in	Product Weight US	0.06 lb
------------------	--------	-------------------	---------

Product Height US	1.0 in	Product Length US	6.0 in
-------------------	--------	-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Seismic Tested	No	Wire Size	12 AWG
Indoor/Outdoor	Indoor	Connection Type	Plugtail, Wired
Environmental Conditions	0 to 95% (relative humidity, non-condensing)		