



## Pass and Seymour PlugTail® Switch Right Angle Connector 3-Wire, 6" Stranded THHN12 Part No. PTS6STR3



PlugTail information, visit our PlugTail Headquarters.

### Features & Benefits

All PlugTail: Connectors are available in any wire length up to 25 inches

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Audible snapping latch assures connection, allows release.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Large crimped and welded brass contacts

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### Specifications

#### General Info

UPC Number	785007108170	Country Of Origin	Mexico
------------	--------------	-------------------	--------

Product Line	Pass & Seymour	Application Sector	Industrial
--------------	----------------	--------------------	------------

Standard	UL 498/20
----------	-----------

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

#### Technical Information

Number of Poles	Single Pole	Voltage	120 V
-----------------	-------------	---------	-------

Contact Rating	120/277Vac	Action	Single pole
----------------	------------	--------	-------------