



Pass and Seymour
PlugTail® Switch Right Angle Connector 3-Wire, 6-in Stranded THHN12
Part No. PTS6STR3



PlugTail® Switch Right Angle Connector 3-Wire, 6-inch Stranded THHN12

Features & Benefits

All PlugTail: Connectors are available in any wire length up to 25 inches

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Audible snapping latch assures connection, allows release.

For covering patents, see www.legrand.us/patents.

Large crimped and welded brass contacts

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007108170	Country Of Origin	Mexico
Features	Stranded Conductors	Application Sector	Commercial, Industrial
Wall Plate Included	No	Standard	UL 498/20
Warranty Type	1-Year Limited Warranty	Type	Plug Tail Connector

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Connection Location	Back Only	Terminal Accommodation	#14 AWG - #12 AWG
Number of Gangs	1	Number of Poles	Single Pole
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Snap-in	Wire Connection Type	Flying Leads
Voltage	120.0 V		