



- PlugTail® Switch, Right Angle Connector, 3-Wire, 277V, Stranded, 6-inch PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each switch. Utilizes XHHW-2 wire.

## Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.	Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
Utilizes XHHW-2 wire which is a thermoset insulated with XLPE (cross-linked Polyethylene).	Ideal connectors for fast and secure wire termination.
Substantially higher insulation resistance than THHN wire and does not have PVC in insulation.	Ideal for projects requesting that products be free of any components on Red List.
Wire temperature rated 90°C Wet/Dry.	PlugTail™ Connector: #12 AWG, XHHW - 2, copper conductor, 6 - in leads, stripped, stranded, for use with PlugTail Switches only

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Yellow	Country Of Origin	Mexico
Construction	Injection molded plastic	Features	Plug-In, Right Angle
Package Quantity	1	Application Sector	Commercial
Standard	RoHS, cULus	Warranty Type	1-Year

### Dimensions

Product Width US	1.0 in	Product Weight US	0.06 lb
Product Height US	1.0 in	Product Length US	6.0 in

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

---

## Additional Information

---

RoHS Conformant      Yes

---

## Technical Information

---

Wire Size      12 AWG      Indoor/Outdoor      Indoor

---

Connection Type      Plugtail, Wired      Environmental Conditions      0 to 95% (relative humidity, non-condensing)

---