



Pass and Seymour
PlugTail® Switch, Right Angle Connector, 3-Wire, Stranded, 6-in XHHW-2 Wire
Part No. PTS6STR3X2



PlugTail® Switch, Right Angle Connector, 3-Wire, Stranded, 6-inch PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each switch. Utilizes XHHW-2 wire.

Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Utilizes XHHW-2 wire which is a thermoset insulated with XLPE (cross-linked Polyethylene).

Substantially higher insulation resistance than THHN wire and does not have PVC in insulation.

Ideal for projects requesting that products be free of any components on Red List.

Wire temperature rated 90°C Wet/Dry.

PlugTail™ Connector: #12 AWG, XHHW - 2, copper conductor, 6 - in leads, stripped, stranded, for use with PlugTail Switches only

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007432916	Country Of Origin	Mexico
Features	Plug-In, Right Angle	Application Sector	Commercial
Standard	RoHS, cULus	Warranty Type	1-Year

Dimensions

Product Width US	1.0 in	Product Weight US	0.06 lb
Product Height US	1.0 in	Product Length US	6.0 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Seismic Tested	No	Wire Size	12 AWG
Indoor/Outdoor	Indoor	Connection Type	Plugtail, Wired
Environmental Conditions	0 to 95% (relative humidity, non-condensing)		