



PlugTail® Switch Right Angle with WAGO Connector 4-Wire, 6-inch Stranded THHN12 for 277V Applications

Features & Benefits

All PlugTail: Connectors are available in any wire length up to 25 inches

Large crimped and welded brass contacts

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Audible snapping latch assures connection, allows release.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007001242
--------------	----------------	------------	--------------

Country Of Origin	Mexico
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----