



Pass and Seymour
PlugTail® Switch Right Angle Connector, 4-Wire, Stranded, 6-in XHHW-2 Wire
Part No. PTS6STR4X2



PlugTail® Switch, Right Angle Connector, 4-Wire, Stranded, 6-inch PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each switch. Utilizes XHHW-2 wire.

Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

Utilizes XHHW-2 wire which is a thermoset insulated with XLPE (cross-linked Polyethylene).

Substantially higher insulation resistance than THHN wire and does not have PVC in insulation.

Ideal for projects requesting that products be free of any components on Red List .

Wire temperature rated 90°C Wet/Dry.

PlugTail™ Connector: #12 AWG, XHHW - 2, copper conductor, 6 - in leads, stripped, stranded, for use with PlugTail Switches only

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Yellow	Country Of Origin	Mexico
Construction	Injection molded plastic	Features	Plug-In, Right Angle
Package Quantity	1	Application Sector	Commercial
Standard	RoHS, cULus	Warranty Type	1-Year

Dimensions

Product Width US	1.0 in	Product Weight US	0.06 lb
------------------	--------	-------------------	---------

Product Height US	1.0 in	Product Length US	6.0 in
-------------------	--------	-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Wire Size	12 AWG	Indoor/Outdoor	Indoor
-----------	--------	----------------	--------

Connection Type	Plugtail, Wired	Environmental Conditions	0 to 95% (relative humidity, non-condensing)
-----------------	-----------------	--------------------------	--
