



Pass and Seymour
Discontinued - PlugTail® Hospital Grade 15A USB Charging Receptacles, Light Almond
Part No. PTTR15HACUSBLA



PlugTail® Hospital Grade USB Charging Receptacles provide the convenience of mobile charging without the need for a bulky AC adapter. This device is a perfect match for the constant needs of today's mobile environment and is rugged enough to withstand hard-use commercial applications. It comes equipped with two UL Fed Spec AC receptacles and two USB charging ports for mobile devices - one Type-A port and one Type-C port for newer products. An efficient, 15.5W power supply provides ample power needed for charging mobile phones and tablets. The PlugTail termination provides a more productive, secure, and safer installation and allows you to connect with the future of wiring device innovations.

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

Features & Benefits

AC receptacles are tamper resistant as standard : patented shutter system prevents improper insertion of foreign objects	Efficient, 15.5W power supply for fast charging of mobile phones and tablets
Triple-wipe, brass line contacts for 15A commercial applications	Multiple color options available
Zinc-plated steel for corrosion resistance	5Vdc Type-C USB port to charge USB Type-C compatible mobile devices
PlugTail termination allows for more productive, finger-safe installation and added future flexibility	Stainless steel auto-ground clips assure positive ground
Available in 15 & 20A, Specification Grade and Hospital Grade configurations	

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	PTTR15HACUSBLA
Color	Light Almond	Country Of Origin	China

Dimensions

Product Width US	1.693 in	Product Depth US	1.45 in
Product Height US	2.677 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

USB Amperage	3.1 A	USB Power Output	15 W
Amperage	15 A		
